

MAGNUM VENUS PRODUCTS

SE Advantage 2000 Glecoat Unit	85812-1
--------------------------------	---------

REV. A = MODIFIED DESIGN TO ACCOMMODATE MULTIPLE UNITS 6/18/02 JEM
 B = ITEM 9 WAS 85851-9 11/16/04 JEM

SE Advantage 2000 Gelcoat Unit 85812-1


PARTS LIST

ITEM	PART NO.	QTY	DESCRIPTION
1	85710-3	1	PUMP ASSEMBLY
2	85703-3	1	PRO CAT PUMP W/RECIRC
3	VHSA-1000	1	SUCTION WAND ASSY
4	FF-5000R-100	1	RESIN FILTER ASSY
5	SC-2510	1	ACCUMULATOR ASSY
6	60477-1	1	RESIN HEATER ASSY
7	4105-00-01	1	2 GAL CAT JUG W/RECIRC
8	5111-04-01-INT	1	GUN ASSY
9	MA-ADV-1	1	MANIFOLD ASSY
10	6502-05-030	1	3/8 ADVANTAGE HOSE SET
11	55207-1	1	3 GAL FLUSH TANK ASSY
12	85770-69	1	PUMP MOUNT - GELCOAT PUMP
13	85829-1	1	MANIFOLD MOUNT BRACKET
14	85730-1	1	CAT JUG BRKT WELD
15	3106-12-5	1	TOP HEATER GUARD
16	6509-01-030	1	ASSY - 3/8" x 30' RESIN HOSE W/WHIP
17	6504-21-04	1	ASSY - 3/8" x 4' RESIN HOSE
18	6504-18-06	1	1/4" x 6' SINGLE END RESIN HOSE
19	6101-4-01	1	FLUSH TANK MOUNT BRACKET
20	59553-1	1	ASSY - DRUM GROUND CABLE
21	01418-5	1	3/8" x 5' CLEAR POLY TUBING
22	01446-8	1	1/4" x 8' RED POLY TUBING
23	6703-02-020	1	ASSY - 20' EARTH GROUND CABLE
24	85873-1	1	HOSE RACK
25	01754-1	1	ASSY - 3/8" x 42" AIR HOSE
26	15656	1	1/4" BALL VALVE
27	6504-10-030	1	1/4" GREEN POLY TUBE
	00018	1	NIPPLE
	00271	1	CLOSE NIPPLE
	00443	1	CROSS
	02650-7	3	HEX CAP SCREW
	05819	1	BALL VALVE
	05829-1	2	HOSE FITTING
	05840	1	PIPE FITTING
	07331	1	CONNECTOR
	07455	1	FILTER SCREEN
	07652	1	QUICK EXHAUST
	08936	2	FEMALE QUICK DISCONNECT
	08937	2	MALE QUICK DISCONNECT
	7101-1-3	1	HEX CAP SCREW
	F-HB-06C-16	8	HEX CAP SCREW
	7201-6-4	3	HEX NUT
	F-HN-06C	3	HEX NUT
	7202-4-12	3	LOCK WASHER
	7701-1-1	1	ELBOW
	7701-1-2	1	ELBOW
	7701-1-8	1	ELBOW
	7701-3-17	1	NIPPLE
	TRU-1021	1	FITTING
	7701-6-16	1	POLY FITTING
	7701-6-17	1	POLY FITTING
	7701-6-7	1	BARB FITTING

PARTS LIST

PART NO.	QTY	DESCRIPTION
BV-44-HP	1	BALL VALVE
85721-1	1	FILTER BODY
VPA-1000	1	AIR ASSIST ASSY
00383	1	MALE CONNECTOR
6504-11-030	1	1/4" CLR POLY TUBE
6504-2-0.5	1	1/4" X6" RESIN WHIP
6504-5-030	1	CAT HOSE ASSY
6504-7-030	1	HOSE ASSY
6506-1-0.5	1	3/8" POLY WHIP
6703-2-030	1	30' GRD WIRE
85735-1	1	SPARES KIT
TLS-800	1	TSL, I PNT
90065-1	1	MANUAL
90072-1	1	MANUAL
M6707-1-1	1	MANUAL
12017	1	MANUAL

FIGURE 1-1



NOTE:

1. SEE ALSO DOCUMENT #90072-1, PROCEDURE FOR INSTALLATION
2. CATALYST JUG MUST BE A MINIMUM OF SIX INCHES ABOVE PUMP, AND A MAXIMUM OF TWELVE INCHES (1-FOOT) FROM THE PUMP MOUNT TO BOTTOM CENTER OF CATALYST JUG.
3. CATALYST FEED LINE MUST NEVER DROP LOWER THAN THE INLET FITTING ON THE CATALYST PUMP
4. MOUNT UNIT TO PANEL, THEN MOUNT PANEL TO THE WALL.
5. MOUNT 85873-1 HOSE RACK WHEREVER CONVENIENT FOR HOSE STORAGE